

# **Digital MCH**

Photopolymer Plates





### Low Dot Gain And Smooth Ink Laydown From One Plate.

With Digital MCH, MacDermid expands its capped plate offering by providing a new 60 durometer, capped plate for those printers seeking the best of high end, full-color process printing.

Digital MCH offers a unique mirco-rough surface for excellent ink transfer, creating fine imaging detail. The innovative cap layer ensures that the plate provides the besttonal range possible. And because it is wear resistant, you are guaranteed long run durability on press.

For performance that makes your flexo printing consistent and you platemaking simple, count on the company that innovates with you in mind. MacDermid.

#### **KEY FEATURES**

- Solvent or thermal processing
- Excellent imaging with the lowest dot gain
- A balanced plate surface for low image gain and exceptional solids coverage
- Incredible durability
- Ozone resistant
- Runs clean time and time again

#### **SEGMENTS**

- Flexible Packaging
- Tags and Labels



• Folding Carton



• Sacks, Paper, Multiwall



## Digital MCH

### Photopolymer Plates



#### **TECHNICAL SPECIFICATIONS**

Digital MCH is available in thicknesses of 0.045" (1.12mm) -0.107" (2.71mm) and in sizes up to 52" x 80"(1,320mm x2,032mm). Please contact your MacDermid representative for details.

Digital MCH has a hardness of 60 Shore A.

#### REPRODUCTION CAPABILITIES

 Halftones:
 0.5 - 99% at 200 lpi (80 lines/cm)

 Fine lines:
 0.001 in. (0.025 mm) width

 Isolated dots:
 0.005 in. (0.127 mm diameter)

Fine lines and isolated dots using 0.067 (1.70mm) plate

#### **PLATE PROCESSING\***

Digital MCH can be processed in either solvent or thermal systems. For solvent processing, use with SOLVIT® M100 or SOLVIT® QD is recommended. Most other safe-solvent solutions may be used.

Processing times for any particular job are determined by equipment, copy requirements, and plate thickness.

#### **INK/SOLVENT COMPATIBILITY**

Digital MCH photopolymer is compatible with UV, alcohol, water, and glycol-based inks. Digital MCH is not recommended for use with oil-based inks or hydrocarbon solvents.

#### **APPLICATIONS**

Digital MCH is recommended for high quality printing on film and preprint liner, particularly for process color. Digital MCH can also be used successfully in other applications such as high quality labels and folding cartons.



#### RECOMMENDED PROCESSING CONDITIONS\*

GAUGE	DUROMETER	DESIRED RELIEF	BACK EXPOSURE <sup>1,2</sup>		FACE EXPOSURE <sup>2</sup>		WASH OUT <sup>3</sup>	DRY TIME	POST EXPOSURE <sup>3</sup>	DETACK <sup>4</sup>
(mil/mm)	(Shore A)	(mil/mm)	(mJ/cm²)	(sec)	(J/cm²)	(min)	(sec)	(hrs)	(min)	(min)
45/1.14	78	18-22	1540	140	9	10	240	120	5	5
67/1.70	71	18-22	2100	190	9	10	300	120	5	5

<sup>\*</sup>Contact your MacDermid representative for assistance in establishing proper processing conditions

- 1. For thermally processed plates, back exposure time is 15-30% less than for solvent processed plates
- 2. Lamp intensity 15 mW for top lamps, 11 mW for lower lamps
- 3. Solvit QD washout times



**EUROPE** 

USA 5210 Phillip Lee Drive Atlanta, GA 30336 P 404.696.4565

3 rue de l'Industrie - BP 30160 68702 Cernay Cedex, France P+33 (0) 3 89 38 43 12